

**AVIT - Hochdruckrohrtechnik** - High Pressure Tubing Technique, Wlding Screw Connections

**1 - Spare parts, Welding cones, nuts**



AK - Welding cone



AKM - Welding cone with nut



ARK - Welding cone - pipe size



AKS - Welding cone with nut - pipe size



ARK - Reduced welding cone



DKS - Double cone



VK - Lock cone



M - Nut

**2 - Male couplings**



GEV - Male stud coupling



GUV - Male stud coupling with U-ring sealing



GOV - Male stud coupling with O-ring



GEAM/GEVA - Male stud coupling



GUR - Reducing male coupling



GUG - Male coupling with larger thread



GUL - Adjustable male stud for combinations



GELM/GELA - Adjustable male stud for combinations



DU - Double-ended nipple



DN - Double-ended nipple



DO - Double-ended nipple



SV - Adjustable swivel connection throttle free



WS - Stud for combinations



TS - Equal tees



SKV - Swivel connection



TSKV - T swivel connection



RI - Reducing piece



RI - Reducing piece



VSU - Pipe plug

### **3 - Welding couplings**



GAV - Straight welding bosses



AV - Welding fittings



GV Straight couplings



WV - Equal elbows



TV - Equal Tees



KV - Equal crosses



GSV - Straight bulkhead connection



WSV - Bulkhead elbows

### **4 - Pressure test couplings - valves**



DEV - Pressure test and ventilation coupling



MIAK - Pressure test and ventilation coupling



RV - Non return valves



ERV - Non return valves



RRV - Non return valves



RVS - Non return valves



BKH - Ball valve



BKF - Ball valve



[BKS - Ball valve with SAE flanges](#)

## 5 - High pressure flanges



[FA - Flanges - PN 10-64 / series 0](#)



[FK - Flanges - PN 10-64 / series 0](#)



[FA - Flanges - PN 160 / series 2](#)



[FK - Flanges - PN 160 / series 2](#)



[FA - Flanges - PN 250 / series 3](#)



[FK - Flanges - PN 250 / series 3](#)



[FA - Flanges - PN 315 / series 4](#)



[FK - Flanges - PN 315 / series 4](#)



[FA - Flanges - PN 400 / series 5](#)



[FK - Flanges - PN 400 / series 5](#)



[FA - Flanges - PN 500 / series 6](#)



[FK - Flanges - PN 500 / series 6](#)



[FFA - Flanges - PN 250 / series 3](#)



[FFK - Flanges - PN 250 / series 3](#)



[FFA - Flanges - PN 400 / series 5](#)



[FFK - Flanges - PN 400 / series 5](#)



[FV - Flange distributors](#)



[WFA - Flange elbow](#)



[DFA - Welding neck flanges DIN 2633 - PN 16](#)



[DFK - Welding neck flanges DIN 2633 - PN 16](#)



[KOR - Welded reductions](#)

## 6 - SAE flanges



[AFA - SAE flanges with welding piece](#)



[AFKV - SAE flanges with welding piece](#)



[AFE - SAE BSP thread flanges](#)



[AFLA - SAE socket weld flanges](#)



[AFL - SAE socket weld flanges](#)



[AFSA - SAE butt weld flanges](#)



[AFS - SAE butt weld flanges](#)



[AFM - SAE connection 24° AVIT-cones](#)



[AFW - SAE flange elbow butt welding](#)



[AFMW - SAE flange elbow connection 24° AVIT-cones](#)



[AFWA - SAE elbow connection 24° cone with split flange halves](#)